




# AFC FAN AIR CERAMIC

Ugelli antideriva  
Low drift nozzles  
Boquillas antideriva

COD.	 bar	 drop	 l/min	l/ha (spazio tra gli ugelli: 50 cm) l/ha (nozzle spacing: 50 cm) l/ha (espacio entre las boquillas: 50 cm)							
				6 km/h	8 km/h	10 km/h	12 km/h	14 km/h	16 km/h	18 km/h	20 km/h
AFC11001	2	VC	0.33	65	49	39	33	28	24	22	20
	3	VC	0.40	80	60	48	40	34	30	27	24
	4	VC	0.46	92	69	55	46	40	35	31	28
	5	C	0.52	103	77	62	52	44	39	34	31
	6	C	0.57	113	85	68	57	48	42	38	34
AFC110015	2	VC	0.49	98	73	59	49	42	37	33	29
	3	VC	0.60	120	90	72	60	51	45	40	36
	4	C	0.69	139	104	83	69	59	52	46	42
	5	C	0.77	155	116	93	77	66	58	52	46
	6	M	0.85	170	127	102	85	73	64	57	51
AFC11002	2	VC	0.65	131	98	78	65	56	49	44	39
	3	VC	0.80	160	120	96	80	69	60	53	48
	4	VC	0.92	185	139	111	92	79	69	62	55
	5	C	1.03	207	155	124	103	89	77	69	62
	6	C	1.13	226	170	136	113	97	85	75	68
AFC110025	2	VC	0.82	163	122	98	82	70	61	54	49
	3	VC	1.00	200	150	120	100	86	75	67	60
	4	C	1.15	231	173	139	115	99	87	77	69
	5	C	1.29	258	194	155	129	111	97	86	77
	6	C	1.41	283	212	170	141	121	106	94	85
AFC11003	2	VC	0.98	196	147	118	98	84	73	65	59
	3	VC	1.20	240	180	144	120	103	90	80	72
	4	VC	1.39	277	208	166	139	119	104	92	83
	5	C	1.55	310	232	186	155	133	116	103	93
	6	C	1.70	339	255	204	170	145	127	113	102
AFC11004	2	VC	1.31	261	196	157	131	112	98	87	78
	3	VC	1.60	320	240	192	160	137	120	107	96
	4	VC	1.85	370	277	222	185	158	139	123	111
	5	C	2.07	413	310	248	207	177	155	138	124
	6	C	2.26	453	339	272	226	194	170	151	136
AFC11005	2	VC	1.63	327	245	196	163	140	122	109	98
	3	VC	2.00	400	300	240	200	171	150	133	120
	4	VC	2.31	462	346	277	231	198	173	154	139
	5	VC	2.58	516	387	310	258	221	194	172	155
	6	C	2.83	566	424	339	283	242	212	189	170
AFC11006	2	VC	1.96	392	294	235	196	168	147	131	118
	3	VC	2.40	480	360	288	240	206	180	160	144
	4	VC	2.77	554	416	333	277	238	208	185	166
	5	VC	3.10	620	465	372	310	266	232	207	186
	6	C	3.39	679	509	407	339	291	255	226	204

	DIMENSIONE DELLE GOCCE DROP SIZE RATING DIMENSIONES DE LAS GOTAS	
M	Media-Medium-Media	217µm ÷ 353µm
C	Grossa-Coarse-Gruesa	354µm ÷ 464µm
VC	Molto grossa-Very coarse-Muy gruesa	> 464µm

millesimo di millimetro (Es.: 250µm = 0.25 mm)  
µm= thousandth of millimeter (E.g.: 250µm = 0.25 mm)  
milésimo de milímetro (Ej.: 250µm = 0.25 mm)